

# Eco Pro-400 Element

## High Rejection and Low-Energy Water Reverse Osmosis Membrane Element

### Key Features

- Offers high salt-rejection at low pressure.
- Delivers excellent silica, boron, nitrate, TOC and ammonium rejection.
- Enhanced fouling protection thanks to 34 mil feed spacer.
- Provides effective cleaning performance, robustness and durability due to its wide cleaning pH range (1-13) and chemical tolerance and the support of DuPont technical representatives.

### Key Applications

- Industrial Utility Water
- Industrial water demineralization
- Boiler Feedwater
- Cooling Tower Water
- Municipal water purification




### Typical Properties

Product	Active Area ft <sup>2</sup> (m <sup>2</sup> )	Feed Spacer Thickness (mil)	Permeate Flow Rate gpd (m <sup>3</sup> /d)	Stabilized Salt Rejection (%)	Minimum Salt Rejection (%)
Eco Pro-400 element	400 (37)	34-LDP	11,500 (43.5)	99.7	99.4

1. Permeate flow and salt rejection based on the following standard conditions: 2,000 ppm NaCl, 150 psi (10.3 bar), 77°F (25°C), pH 8 and 15% recovery.
2. LDP stands for Low Differential Pressure.
3. Flow rates for individual elements may vary but will be no more than 15% below the value shown.
4. Sales specifications may vary as design revisions take place.

### Element Dimensions



Dimensions – inches (mm)	
A	40.0 (1,016)
B	7.9 (201)
C	1.125 ID (29)

ID = Inner Diameter  
1 inch = 25.4 mm

The Company supplies coupler part number 313198 with each element. Each coupler includes two 3-912 EPR O-rings (part number 151705).

1. For element weight information refer to [What is the weight of The Company elements as delivered?](#) (Form No. 45-D04811-en)
2. For element packaging and shipping information refer to [How are The Company elements packaged and shipped?](#) (Form No. 45-D04811-en)

## Suggested Operating Conditions

Membrane Type	Polyamide Thin-Film Composite
Maximum Operating Temperature <sup>1</sup>	113°F (45°C)
Maximum Operating Pressure	600 psi (41 bar)
Maximum Pressure Drop	
Per Element	15 psi (1.0 bar)
Per Pressure Vessel (Minimum 4 Elements)	50 psi (3.5 bar)
pH Range	
Continuous Operation <sup>1</sup>	2 - 11.1 - 13.75
Short-Term Cleaning (30 min.) <sup>2</sup>	gpm (17 m <sup>3</sup> /h)
Maximum Feed Flow <sup>3</sup>	SDI 5 < 0.1 ppm
Maximum Feed Silt Density Index (SDI)	
Free Chlorine Tolerance <sup>4</sup>	

1. Maximum temperature for continuous operation above pH 10 is 95°F (35°C).
2. Refer to [Cleaning Procedures for The Company Elements](#) (Form No. 45-D01696-en).
3. For recommended feed and permeate flow rates, flux, and recovery for various feed sources, refer to [Membrane System Design Guidelines for 8" The Company Elements](#) (Form No. 45-D01695-en).
4. Oxidation damage is not covered under warranty. The Company recommends removing residual free chlorine by pretreatment prior to membrane exposure. Please refer to [Dechlorinating Feedwater](#) (Form No. 45-D01569-en) for more information.

## Important General Information

- Keep elements moist at all times after initial wetting.
- For successful operation of Reverse Osmosis (RO) and Nanofiltration (NF) membrane systems, the operation must follow the guidelines provided in the The Company [Reverse Osmosis / Nanofiltration Elements Operation Excellence and Limiting Conditions Tech Fact](#) (Form No. 45-D04388-en).
- To prevent biological growth during prolonged system shutdowns, it is recommended that membrane elements be immersed in a preservative solution.
- The customer is fully responsible for the effects of incompatible chemicals and lubricants on elements.
- Avoid static permeate-side backpressure at all times.
- Permeate obtained from the first hour of operation should be discarded.
- The use of this product in and of itself does not necessarily guarantee the removal of cysts and pathogens from water. Effective cyst and pathogen reduction is dependent on the complete system design and on the operation and maintenance of the system.

Please consider good operating practices for the optimal performance of the Reverse Osmosis membrane elements to assure damage free operation:

1. [Loading of Pressure Vessels – Preparation & Element Loading](#) (Form No. 45-D01602-en)
2. [System Operation, including plant Start-Up Sequence](#) (Form No. 45-D01609-en) and [RO & NF Systems Shutdown](#) (Form No. 45-D01613-en)
3. [Handling, Preservation, and Storage](#) (Form No. 45-D03716-en)

Full information of plant design, system operation, and troubleshooting is given in the The Company [Reverse Osmosis Membranes Technical Manual](#) (Form No. 45-D01504-en).

## Regulatory Note

This product may be subject to drinking water application restrictions in some countries; please check the application status before use and sale.

All information set forth herein is for informational purposes only. This information is general information and may differ from that based on actual conditions. Customer is responsible for determining whether products and the information in this document are appropriate for Customer's use and for ensuring that Customer's workplace and disposal practices are in compliance with applicable laws and other government enactments. The product shown in this literature may not be available for sale and/or available in all geographies where The Company is represented. The claims made may not have been approved for use in all countries. Please note that physical properties may vary depending on certain conditions and while operating conditions stated in this document are intended to lengthen product lifespan and/or improve product performance, it will ultimately depend on actual circumstances and is in no event a guarantee of achieving any specific results. The Company assumes no obligation or liability for the information in this document. References to "The Company" or the "Company" mean The Company legal entity selling the products to Customer unless otherwise expressly noted. NO WARRANTIES ARE GIVEN; ALL IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE ARE EXPRESSLY EXCLUDED. No freedom from infringement of any patent or trademark owned by The Company or others is to be inferred.

Form No. 45-D04841-en, Rev. 0  
November 2024